

FRONT PANEL, FRONT SHIELDED, SIDE HINGED

Front panel with textile EMC gasket, side hinged assembly.



CERTIFICATIONS



FEATURES

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

SPECIFICATIONS

Table 1/3

| Catalog Number | EMC Gasket Type | Treated Edges | Front Finish | Rear Finish | EMC Shielding | Rack Width |
|----------------|-----------------|---------------|--------------|-------------|--------------------|------------|
| 20848-611 | Textile | No | Anodized | Conductive | No (Retrofittable) | 84 HP |
| 20848-617 | Textile | No | Anodized | Conductive | No (Retrofittable) | 84 HP |

Table 2/3

| Catalog Number | Package Quantity | Height | Product Type | Type | Rack Height | Width |
|----------------|------------------|--------|--------------|------|-------------|-------|
|----------------|------------------|--------|--------------|------|-------------|-------|

| | | | | | | |
|-----------|---|----------|-------------|----------------------------|-----|----------|
| 20848-611 | 1 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 426.4 mm |
| 20848-617 | 1 | 261.8 mm | Front Panel | Front Panel without Handle | 6 U | 426.4 mm |

| Table 3/3 | | |
|----------------|--------------|----------|
| Catalog Number | Mounting | Material |
| 20848-611 | Hinged, Side | Aluminum |
| 20848-617 | Hinged, Side | Aluminum |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.