CRIMPING COMPRESSION TOOL DIE, TYPE ML, STANDARD, 150 MM² STRANDED, 300 KCMIL STRANDED

CATALOG NUMBER

RKML150

FEATURES

Suitable for cable lugs and connectors

PRODUCT ATTRIBUTES

Article Number: 716988
Lug/Connector Type: Standard
Conductor Size: 150 mm² Stranded; 300 kcmil Stranded
Crimping Width: 5mm
Tool: MLB

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.