

LADDER RACK CURVED SECTIONS (CULUS CLASSIFIED)



The Ladder Rack Curved Sections provide a vertical change in direction. They are made of 1-1/2 inch x 3/8 inch (38 mm x 8 mm) tubular steel with a painted or plated finish. Cross members are welded on the inside (inside bends) or outside (outside bends) of the section. They connect to straight section with butt-splice kits. They are also designed for category 5e, 6, 6A and fiber optic cable.

FEATURES

The Ladder Rack Curved Sections provide a vertical change in direction

They are made of 1-1/2 inch x 3/8 inch (38 mm x 8 mm) tubular steel with a painted or plated finish

Cross members are welded on the inside (inside bends) or outside (outside bends) of the section

They connect to straight section with butt-splice kits

They are also designed for category 5e, 6, 6A and fiber optic cable

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Thickness	Vertical Bend Type	Color Code	Color	Material
LIB12BLK	10053	1.52mm	Inside	RAL 9005	Jet Black	Mild Steel
LIB12G	10052	1.52mm	Inside	ANSI 61	Gray	Mild Steel
LIB12GZ	10054	1.52mm	Inside			Mild Steel
LIB12W	29918	1.52mm	Inside		White	Mild Steel
LIB15BLK	29987	1.52mm	Inside	RAL 9005	Jet Black	Mild Steel
LIB15W	29988	1.52mm	Inside		White	Mild Steel
LIB18BLK	10056	1.52mm	Inside	RAL 9005	Jet Black	Mild Steel
LIB18G	10055	1.52mm	Inside	ANSI 61	Gray	Mild Steel
LIB18GZ	10057	1.52mm	Inside			Mild Steel
LIB18W	29922	1.52mm	Inside		White	Mild Steel
LIB24BLK	17337	1.52mm	Inside	RAL 9005	Jet Black	Mild Steel

Catalog Number	Article Number	Thickness	VerticalBend Type	Color Code	Color	Material
LIB24W	29924	1.52mm	Inside		White	Mild Steel
LIB6BLK	10047	1.52mm	Inside	RAL 9005	Jet Black	Mild Steel
LIB6G	10046	1.52mm	Inside	ANSI 61	Gray	Mild Steel
LIB6GZ	10048	1.52mm	Inside			Mild Steel
LIB6W	29916	1.52mm	Inside		White	Mild Steel
LOB12BLK	10038	1.52mm	Outside	RAL 9005	Jet Black	Mild Steel
LOB12G	10037	1.52mm	Outside	ANSI 61	Gray	Mild Steel
LOB12GZ	10042	1.52mm	Outside			Mild Steel
LOB12W	29921	1.52mm	Outside		White	Mild Steel
LOB15BLK	29985	1.52mm	Outside	RAL 9005	Jet Black	Mild Steel
LOB15W	29986	1.52mm	Outside		White	Mild Steel
LOB18BLK	10044	1.52mm	Outside	RAL 9005	Jet Black	Mild Steel
LOB18G	10043	1.52mm	Outside	ANSI 61	Gray	Mild Steel
LOB18GZ	10045	1.52mm	Outside			Mild Steel
LOB18W	29923	1.52mm	Outside		White	Mild Steel
LOB24BLK	17336	1.52mm	Outside	RAL 9005	Jet Black	Mild Steel
LOB24W	29925	1.52mm	Outside		White	Mild Steel
LOB6BLK	10035	1.52mm	Outside	RAL 9005	Jet Black	Mild Steel
LOB6G	10034	1.52mm	Outside	ANSI 61	Gray	Mild Steel
LOB6GZ	10036	1.52mm	Outside			Mild Steel
LOB6W	29917	1.52mm	Outside		White	Mild Steel

Table 2/2		
Catalog Number	Article Number	Finish
LIB12BLK	10053	Powder Coated
LIB12G	10052	Powder Coated
LIB12GZ	10054	Zinc Plated
LIB12W	29918	Powder Coated
LIB15BLK	29987	Powder Coated
LIB15W	29988	Powder Coated
LIB18BLK	10056	Powder Coated
LIB18G	10055	Powder Coated
LIB18GZ	10057	Zinc Plated
LIB18W	29922	Powder Coated
LIB24BLK	17337	Powder Coated

Catalog Number	Article Number	Finish
LIB24W	29924	Powder Coated
LIB6BLK	10047	Powder Coated
LIB6G	10046	Powder Coated
LIB6GZ	10048	Zinc Plated
LIB6W	29916	Powder Coated
LOB12BLK	10038	Powder Coated
LOB12G	10037	Powder Coated
LOB12GZ	10042	Zinc Plated
LOB12W	29921	Powder Coated
LOB15BLK	29985	Powder Coated
LOB15W	29986	Powder Coated
LOB18BLK	10044	Powder Coated
LOB18G	10043	Powder Coated
LOB18GZ	10045	Zinc Plated
LOB18W	29923	Powder Coated
LOB24BLK	17336	Powder Coated
LOB24W	29925	Powder Coated
LOB6BLK	10035	Powder Coated
LOB6G	10034	Powder Coated
LOB6GZ	10036	Zinc Plated
LOB6W	29917	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER