

## NVENT CADDY CAT CM U-HOOK



### CERTIFICATIONS



### FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

System offers a convenient pathway for wires and cables

Specially designed U-Hooks have large-diameter, rounded support surfaces

U-Hooks can be mounted vertically along the same drop rod to create a tree configuration

Cantilever mounting allows U-Hooks to be mounted to walls and columns with brackets

Rounded edges help prevent over-bending and kinking of cables

Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure

Compliant with NEC® and ANSI®/TIA structured cabling systems standards

### SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel


Table 1/2

Catalog Number	Cable Capacity, Cat 6A	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	A	Hole Size (HS)	Area
CAT200CMLN	215	450	350	203mm	9.5mm	533mm <sup>2</sup>
CAT300CMLN	325	700	525	304mm	9.5mm	812mm <sup>2</sup>

Table 2/2

Catalog Number	Static Load (F)
CAT200CMLN	440N
CAT300CMLN	440N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**