

VARISTAR CP DOUBLE GLAZED DOOR, IP 20, 3-POINT LOCKING

FEATURES

Lever handle with key insert (2 keys)

Frame, St, 1.5 mm

Opening angle 180°

Security glass, 6 mm

Can be retrofitted with DIN profile half cylinder

Ingress protection class IP 20

Standard fitting, lock on right-hand door

SPECIFICATIONS

Table 1/2

Catalog Number	Locking Type	Height	Product Type	Product Family	Type	Rack Height
21630-686	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Glass Double Door	24 U
21630-687	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Glass Double Door	24 U
21630-688	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Glass Double Door	29 U
21630-689	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Glass Double Door	29 U
21630-690	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Glass Double Door	33 U
21630-691	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Glass Double Door	33 U
21630-692	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Glass Double Door	38 U
21630-693	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Glass Double Door	38 U

Catalog Number	LockingType	Height	ProductType	Product Family	Type	Rack Height
21630-694	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Glass Double Door	42 U
21630-695	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Glass Double Door	42 U
21630-696	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Glass Double Door	47 U
21630-697	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Glass Double Door	47 U

Table 2/2				
Catalog Number	Width	Color	Color Code	Protection Rating
21630-686	600 mm	Black Grey	RAL 7021	IP20
21630-687	800 mm	Black Grey	RAL 7021	IP20
21630-688	600 mm	Black Grey	RAL 7021	IP20
21630-689	800 mm	Black Grey	RAL 7021	IP20
21630-690	600 mm	Black Grey	RAL 7021	IP20
21630-691	800 mm	Black Grey	RAL 7021	IP20
21630-692	600 mm	Black Grey	RAL 7021	IP20
21630-693	800 mm	Black Grey	RAL 7021	IP20
21630-694	600 mm	Black Grey	RAL 7021	IP20
21630-695	800 mm	Black Grey	RAL 7021	IP20
21630-696	600 mm	Black Grey	RAL 7021	IP20
21630-697	800 mm	Black Grey	RAL 7021	IP20

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER