



BC200-CD CONDUIT TO BEAM CLAMP



CERTIFICATIONS



FEATURES


- Eliminates offset bending conduit
- Threaded hole on back
- Ideal for electrical, mechanical, and HVAC applications

SPECIFICATIONS

Table 1/2						
Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)
BC200CD1B	182220	Steel	Electrogalvanized	19 - 25 mm	16 mm Max	6

Table 2/2			
Catalog Number	Article Number	Torque (TQ)	Static Load (F)
BC200CD1B	182220	4 N·m	440N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER