


## CANTILEVER ARM WITH EOL CHANNEL



### CERTIFICATIONS



### FEATURES

Perforated, cold rolled

Slotted backplate

### SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/1

Catalog Number	Article Number	Length (L)
CE0L13H0180EG	599879	180 mm
CE0L13H0300EG	599880	300 mm

**Thickness (T):** 1.25 mm


**E:** 4 mm

**Y:** 8.5 x 20 mm

**Hole Size (HS):** 10.5 mm

<b>X:</b>	11 x 18 mm
<b>C:</b>	15.5 mm
<b>A:</b>	18 mm
<b>B:</b>	27 mm
<b>Width (W):</b>	40 mm
<b>D:</b>	60 mm
<b>Height (H):</b>	120 mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**