



510 NVENT CADDY EZ RISER, S304, 10" PIPE, 250 DN, 273 MM OD

CATALOG NUMBER

5101000S4



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

FEATURES

Only one tool needed to tighten due to serrated wash-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

PRODUCT ATTRIBUTES

Material: Stainless Steel 304 (EN 1.4301)

Pipe Size: 10"

NB/DN: 250

Outer Diameter (OD): 273 mm

Hole Size (HS): 17 mm

A: 524 mm

B: 51 mm

Static Load (F): 11100N

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER