



## HD NI HEAVY DUTY PIPE CLAMP, FIRE/SPRINKLER, EG, 20–24 MM OD, 1/2" PIPE, 15 DN, M8, M10 ROD

### CATALOG NUMBER

**HDN024**



### CERTIFICATIONS



### FEATURES

Fillet welded connector nut has flats to accommodate spanners

Flared steel band also suitable for plastic pipe

Easy open flange for pipe sizes up to and including 4"

### PRODUCT ATTRIBUTES

Article Number: 577002

Nut Included: Yes

Material: Steel

Finish: Electrogalvanized

Outer Diameter (OD): 20 - 24 mm

Pipe Size: 1/2"

NB/DN: 15


Rod Size (RS): 8;10

Width (W): 30 mm

Thickness (T): 2.5 mm

Static Load (F): 2000N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**