



## NVENT CADDY MACROFIX NON-INSULATED M8/M10, 270–280 MM OD, 10" PIPE, 250 DN

### CATALOG NUMBER

**MFN280EG**



### CERTIFICATIONS



### FEATURES

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

### PRODUCT ATTRIBUTES

Article Number: 586124

Material: Steel

Finish: Electrogalvanized

Outer Diameter (OD): 270 - 280 mm

Pipe Size: 10"

NB/DN: 250

Rod Size (RS): 8;10

Width (W): 30 mm


Thickness (T): 2.5 mm

Screw Diameter (Sc): 6

Screw Length (L): 32mm

Static Load (F): 4000N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.