



EM-M CONDUIT/PIPE TO FLANGE CLIP



CERTIFICATIONS



FEATURES

- Supports conduit/pipe or cable from beam flanges
- Snap close clip pivots a full 360°
- Requires only a hammer to install


SPECIFICATIONS

Finish: nVent CADDY Armour

Table 1/1						
Catalog Number	Article Number	Material	Outer Diameter (OD)	Flange Thickness (FT)	Static Load (F)	Certifications
16EM24	171740	Spring Steel	23.4 - 35 mm	3 - 8 mm	330N	ITB
20EM24	171800	Spring Steel	35 - 42 mm	3 - 8 mm	330N	ITB
24EM24	171960	Spring Steel	42 - 50 mm	3 - 8 mm	330N	ITB
32EM24	173600	Spring Steel	50 - 60 mm	3 - 8 mm	330N	ITB
812EM24	160120	Spring Steel	18 - 30 mm	3 - 8 mm	330N	ITB

Catalog Number	Article Number	Material	Outer Diameter (OD)	Flange Thickness (FT)	Static Load (F)	Certifications
8EM24S1	179780	Stainless Steel 301 (EN 1.4310)	18 - 22 mm	3 - 8 mm	200N	
12EM58S1	179820	Stainless Steel 301 (EN 1.4310)	22 - 30 mm	8 - 14 mm	200N	
16EM58	171490	Spring Steel	23.4 - 35 mm	8 - 14 mm	330N	ITB
20EM58	171950	Spring Steel	35 - 42 mm	8 - 14 mm	330N	ITB
24EM58	171970	Spring Steel	42 - 50 mm	8 - 14 mm	330N	ITB
32EM58	173610	Spring Steel	50 - 60 mm	8 - 14 mm	330N	ITB
6EM58	171750	Spring Steel	14 - 18 mm	8 - 14 mm	330N	
812EM58	160130	Spring Steel	18 - 30 mm	8 - 14 mm	330N	ITB
8EM58S1	179790	Stainless Steel 301 (EN 1.4310)	18 - 22 mm	8 - 14 mm	200N	
12EM912S1	179830	Stainless Steel 301 (EN 1.4310)	22 - 30 mm	14 - 20 mm	200N	
16EM912	173570	Spring Steel	23.4 - 35 mm	14 - 20 mm	330N	ITB
20EM912	173580	Spring Steel	35 - 42 mm	14 - 20 mm	330N	ITB
24EM912	173590	Spring Steel	42 - 50 mm	14 - 20 mm	330N	ITB
32EM912	173620	Spring Steel	50 - 60 mm	14 - 20 mm	330N	ITB
812EM912	160140	Spring Steel	18 - 30 mm	14 - 20 mm	330N	ITB
8EM912S1	179800	Stainless Steel 301 (EN 1.4310)	18 - 22 mm	14 - 20 mm	200N	
812EM1318	160075	Spring Steel	18 - 30 mm	21 - 28 mm	330N	cUL, UL
16EM1318	173745	Spring Steel	23.4 - 35 mm	21 - 28 mm	330N	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER