



THREAD INSTALL ROD HANGER WITH ANGLE BRACKET



FEATURES

Suspends threaded rod from horizontal structures such as laminated wood or concrete beams, joists, ceilings and walls

SPECIFICATIONS

- Finish:** nVent CADDY Armour;Pregalvanized
- Material:** Spring Steel;Steel


Table 1/1						
Catalog Number	Article Number	Hole Size 1 (HS1)	Hole Type 1	Hole Size 2 (HS2)	Hole Type 2	Static Load (F)
M10TIB	175030	7 mm	Plain	10 mm	Threaded	700N
M6TIB	174850	7 mm	Plain	6 mm	Threaded	700N
M8TIB	174940	7 mm	Plain	8 mm	Threaded	700N

ADDITIONAL PRODUCT DETAILS

Loads indicated are for nVent CADDY Fasteners only.

Method of attachment to structure must be evaluated separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER