

CRIMPING COMPRESSION TOOL, BATTERY POWERED, RKM3 SERIES, PKM3 SERIES DIES, #6 STRANDED-800 KCMIL STRANDED, 16 MM² STRANDED-400 MM² STRANDED

CATALOG NUMBER

M3B



FEATURES

Wide cross section range

Ergonomic design

High-performance 18 volt lithium-ion battery for increased work capacity

Automatic retraction stop (ARS) after completed crimping

Lightweight and easy to use

Includes easy-to-carry custom case

PRODUCT ATTRIBUTES

Article Number: 716915

Applied Force: 120kN

System: Battery-powered hydraulic

Dies: RKM3 series; PKM3 series

Crimping Shape: Hexagon

Conductor Size: #6 Stranded - 800 kcmil Stranded; 16 mm² Stranded - 400 mm² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER