

VARISTAR CP STEEL DOOR, PLAIN WITH 3-POINT LOCKING, RAL 7021, 47 U,  
2200H, 600W, IP20

CATALOG NUMBER

**21630-105**



Perforated Varistar CP steel double door with 3-point locking  
for applications with IP 20 protection.

FEATURES

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

PRODUCT ATTRIBUTES

Product Type: Cabinet Door

Product Family: Varistar CP

Type: Steel Door

Works With: Varistar CP

Locking Type: 3-Point Locking

Material: Steel

Finish: Powder Coated

Color: Black Grey

Color Code: RAL 7021

Rack Height: 47U

Height: 2200mm

Width: 600mm

Protection Rating: IP20

Complies With: IEC 61587-1; IEC 61587-3

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

---

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**