

BASIC PDU, EB0311, 230 VAC, 1-PH, 16 A

CATALOG NUMBER

EB0311



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: (12) C13

Socket Quantity: 12

Color: Black

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Finish: Powder Coated

Input Cable Location: Front Feed

Input Current: 16 A

Input Voltage: 200-240 VAC, 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Metering Type: None

Nominal Voltage: 230V
On/Off Switch Included: No
Output Voltage: 230VAC
Plug Type: IEC 60309 316P6 (IP44)
Rack Units: 1U
Removable Input Cable: Yes
Product Family: Enlogic
Type: Basic PDU
Height: 43mm
Package Quantity: 1
Input Cable Length: 3m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.