

## BASIC PDU, EB0313, 230 VAC, 1-PH, 32 A

### CATALOG NUMBER

**EB0313**



Modular, compact PDU. Ultra-Low Profile Design

### FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: (12) C13

Socket Quantity: 12

Color: Black

Switched Outlets: No

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Circuit Breaker Quantity: 2

Finish: Powder Coated

Input Cable Location: Front Feed

Input Current: 32 A

Input Voltage: 200-240 VAC, 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 7.44 kVA

Metering Type: None

Nominal Voltage: 230V

On/Off Switch Included: No

Output Voltage: 230VAC

Plug Type: IEC 60309 332P6 (IP44)

Rack Units: 1U

Removable Input Cable: No

Product Family: Enlogic

Type: Basic PDU

Height: 43mm

Package Quantity: 1

Current Rating: 7.4A

Input Cable Length: 3m

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**