

WLOCK CORD C19/C20, 0.6 M, RED, 100 PCS

CATALOG NUMBER

EP1920R24X100



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

PRODUCT ATTRIBUTES

Product Type: Cable

Product Family: Enlogic

Type: Cable

Works With: RackPower

Length: 600mm

Color: Red

Height: 270mm

Input Cable Length: 0.588m

Package Quantity: 100

Plug Type: C19/C20

Removable Input Cable: No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER