

NVENT CADDY CAT CM DOUBLE J-HOOK



CERTIFICATIONS



FEATURES

- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- System offers a convenient pathway for wires and cables
- Double J-Hooks can be mounted vertically along the same drop rod to create a tree configuration
- Allows addition of cables even when fixed flush to overhead decking
- Specially designed double J-Hook has large-diameter, rounded support surfaces
- Rounded edges help prevent over-bending and kinking of cables
- Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure
- Compliant with NEC® and ANSI®/TIA structured cabling systems standards

SPECIFICATIONS


Table 1/2						
Catalog Number	Article Number	Cable Capacity, Cat 6A	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	A	Hole Size (HS)
CAT100CM	181976	30	70	50	185mm	9.5mm

Table 2/2				
Catalog Number	Article Number	Area	Material	Finish
CAT100CM	181976	80.2mm ²	Steel	Electrogalvanized

ADDITIONAL PRODUCT DETAILS

Area shown is the combined value for both sides. Divide by 2 for area of each side.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER