

SPECIAL TRACK WORK COMPLETE WELDER, SIGNAL



FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Material: Graphite; Steel

Rail Type: Manganese Frog

Table 1/2

| Catalog Number | Bond Terminal Style | Handle Clamp | Conductor Outer Diameter, Nominal | Handle Length | Welder Style | Welding Material |
|----------------|---------------------|------------------------|-----------------------------------|---------------|--------------|-----------------------|
| SBTBTB4B | 3/4" Tab | B323W, Sold Separately | 4.76mm | 381mm | TB4 | SB25, Sold Separately |
| SBTBTB4C | 1" Tab | B323W, Sold Separately | 4.76mm | 381mm | TB4 | SB25, Sold Separately |
| SBTBTB4CL | 1" Tab | B323P, Sold Separately | 4.76mm | 584.2mm | TB4 | SB25, Sold Separately |
| SBXSTB4A | 1" Tab | B323W, Sold Separately | 4.76mm | 381mm | TB4 | SB25, Sold Separately |
| SBTBTB4E | 1" Tab | B323W, Sold Separately | 7.94mm | 381mm | TB4 | SB32, Sold Separately |

Table 2/2

| Catalog Number | Conductor Size |
|----------------|------------------|
| SBTBTB4B | 3/16" Bondstrand |
| SBTBTB4C | 3/16" Bondstrand |
| SBTBTB4CL | 3/16" Bondstrand |
| SBXSTB4A | 3/16" Bondstrand |
| SBTBTB4E | 5/16" Bondstrand |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER