

VARISTAR CP STEEL DOOR, PERFORATED WITH 3-POINT LOCKING



Varistar CP perforated steel door, IP 20 with three point locking.

FEATURES

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Locking Type	Protection Rating	Complies With	Product Type	Height
21630-098	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2000mm
21630-099	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2200mm
21630-100	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2450mm
21630-101	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2000mm
21630-102	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2200mm
21630-103	Steel Door, Perforated	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2450mm

Table 2/3

Catalog Number	Works With	Rack Height	Package Quantity	Finish	Material	Color
21630-098	Varistar CP	42U	1	Powder Coated	Steel	Black Grey
21630-099	Varistar CP	47U	1	Powder Coated	Steel	Black Grey
21630-100	Varistar CP	52U	1	Powder Coated	Steel	Black Grey
21630-101	Varistar CP	42U	1	Powder Coated	Steel	Black Grey
21630-102	Varistar CP	47U	1	Powder Coated	Steel	Black Grey
21630-103	Varistar CP	52U	1	Powder Coated	Steel	Black Grey

Table 3/3

Catalog Number	Color Code	Width
21630-098	RAL 7021	600mm
21630-099	RAL 7021	600mm
21630-100	RAL 7021	600mm
21630-101	RAL 7021	800mm
21630-102	RAL 7021	800mm
21630-103	RAL 7021	800mm

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER