

COMPRESSION SLEEVE



FEATURES

- Tin plated for corrosion prevention
- Annealed copper eases the crimping operation
- Contains a positive stop for proper positioning of the cables inside the sleeve

SPECIFICATIONS

Table 1/1					
Catalog Number	Material	Finish	Conductor Size	Length (L)	Tool/Die Type
A2367J	Copper	Tinned	3/16" Stranded	36.5 mm	SBT031DJ Manual Compression Tool/No die required

ADDITIONAL PRODUCT DETAILS

Note: Each sleeve accommodates 3/16" Bondstrand in one end. The other end of the sleeve accommodates the conductor sizes indicated in the above table.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER