

# CRIMPING COMPRESSION TOOL, BATTERY POWERED



## FEATURES

- Wide cross section range
- Ergonomic design
- High-performance 18 volt lithium-ion battery for increased work capacity
- Automatic retraction stop (ARS) after completed crimping
- Lightweight and easy to use
- Includes easy-to-carry custom case

## SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Applied Force	System	Dies	Crimping Shape	Conductor Size
MLB	716920	50kN	Battery-powered hydraulic	RKML series, PKML series	Hexagon	#10 Stranded - 500 kcmil Stranded, 6 mm <sup>2</sup> Stranded - 240 mm <sup>2</sup> Stranded
M3B	716915	120kN	Battery-powered hydraulic	RKM3 series, PKM3 series	Hexagon	#6 Stranded - 800 kcmil Stranded, 16 mm <sup>2</sup> Stranded - 400 mm <sup>2</sup> Stranded

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**