


MAST BRACKET, X SHAPE



FEATURES

For mast-to-mast or pipe-to-mast mounting connections

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Depth (D)	Width (W)
ACF2GS	103100	Steel	28 - 50 mm	28 - 50 mm	40.5mm	121 mm


Table 2/2

Catalog Number	Article Number	Unit Weight
ACF2GS	103100	1.4 kg

ADDITIONAL PRODUCT DETAILS

Diameter 1 and Diameter 2 maximum combined diameter is 80 mm (3.15").

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER