

## 19" PUSHER FAN, 2 U, AXIAL

Fan tray with integrated pusher fan.



### CERTIFICATIONS



### FEATURES

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

### SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage DC	Product Type	Input Voltage AC	Accessory Type
10713-518		Fan Unit	230 V min	Fan unit, 19"
10713-520		Fan Unit	115 V min	Fan unit, 19"
10713-526		Fan Unit	230 V min	Fan unit, 19"
10713-534		Fan Unit	230 V min	Fan unit, 19"
10713-536		Fan Unit	115 V min	Fan unit, 19"
10713-529	24 V min	Fan Unit		Fan unit, 19"
10713-537	24 V min	Fan Unit		Fan unit, 19"

Catalog Number	Input Voltage DC	Product Type	Input Voltage AC	Accessory Type
19713-540		Fan Unit		Fan unit, 19"

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.