


EUROPACPRO 19" SUBRACK KIT FOR BACKPLANE, SHIELDED

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPECIFICATIONS

Product Type: Subrack/Chassis

| Table 1/2 | | | | | | |
|----------------|--------------|------------------------|-----------------|---------------|------------|-----------------|
| Catalog Number | For Mounting | Board Depth | EMC Gasket Type | EMC Shielding | Rack Width | Handle Included |
| 24563-142 | Backplane | 160 mm, 220 mm | Textile | Yes | 84 HP | No |
| 24563-143 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-144 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-145 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-146 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-442 | Backplane | 160 mm, 220 mm | Textile | Yes | 84 HP | No |
| 24563-443 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-444 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-445 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |
| 24563-446 | Backplane | 160 mm, 220 mm, 280 mm | Textile | Yes | 84 HP | No |

| Table 2/2 | | | | | | |
|----------------|------------------|-------------|-----------------|----------|--------|-------------|
| Catalog Number | Package Quantity | Rack Height | Complies With | Mounting | Depth | Static Load |
| 24563-142 | 1 | 3 U | IEC 60297-3-103 | Rack | 235 mm | 11 kgf |
| 24563-143 | 1 | 3 U | IEC 60297-3-103 | Rack | 295 mm | 11 kgf |
| 24563-144 | 1 | 3 U | IEC 60297-3-103 | Rack | 355 mm | 11 kgf |
| 24563-145 | 1 | 3 U | IEC 60297-3-103 | Rack | 415 mm | 11 kgf |
| 24563-146 | 1 | 3 U | IEC 60297-3-103 | Rack | 475 mm | 11 kgf |
| 24563-442 | 1 | 6 U | IEC 60297-3-103 | Rack | 235 mm | 11 kgf |
| 24563-443 | 1 | 6 U | IEC 60297-3-103 | Rack | 295 mm | 11 kgf |
| 24563-444 | 1 | 6 U | IEC 60297-3-103 | Rack | 355 mm | 11 kgf |
| 24563-445 | 1 | 6 U | IEC 60297-3-103 | Rack | 415 mm | 11 kgf |
| 24563-446 | 1 | 6 U | IEC 60297-3-103 | Rack | 475 mm | 11 kgf |

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER