

INTERSCALE FAN HOLDER WITH FANS

Interscale Fan Holder With Fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m³/h.

FEATURES

Fan holder for mounting on bottom of case

Fans are simple to fit to the fan holder using vibration-damping fixing material

Fan holders fix into desktop case with 2 plastic feet or into 19" case with 2 screws

Fan holder cannot be used in conjunction with the mounting plate (instead use mounting plate with integrated fan holder)

For technical data of fans, please see delivery includes

SPECIFICATIONS

Table 1/3

Catalog Number	Input Voltage DC	Max Ambient Temperature	Airflow	Noise Level	Power	Max Static Pressure
24828-105	12 V min	70 °C	10 m³/h	18 dB(A)	0.9 W	
24828-107	12 V min	70 °C	10 m³/h	18 dB(A)	0.9 W	
24828-104	12 V min	70 °C	10 m³/h	18 dB(A)	0.9 W	
24828-205	12 V min	70 °C	19 m³/h	32 dB(A)	2 W	
24828-207	12 V min	70 °C	19 m³/h	32 dB(A)	2 W	
24828-204	12 V min	70 °C	19 m³/h	32 dB(A)	2 W	
24830-102	12 V min					
24828-305	12 V min	70 °C	170 m³/h	43 dB(A)	5.3 W	
24828-307	12 V min	70 °C	170 m³/h	43 dB(A)	5.3 W	
24830-101	12 V min	70 °C	109 m³/h	44.62 dB(A)		95.41 Pa

Table 2/3

Catalog Number	Package Quantity	Height	Product Type	Product Family	Type	Width
24828-105		40 mm	Fan Unit	Interscale	Fan Tray	40 mm
24828-107		40 mm	Fan Unit	Interscale	Fan Tray	40 mm
24828-104		40 mm	Fan Unit	Interscale	Fan Tray	40 mm

Catalog Number	Package Quantity	Height	ProductType	Product Family	Type	Width
24828-205		80 mm	Fan Unit	Interscale	Fan Tray	80 mm
24828-207		80 mm	Fan Unit	Interscale	Fan Tray	80 mm
24828-204		80 mm	Fan Unit	Interscale	Fan Tray	80 mm
24830-102	2	80 mm	Fan Unit		Fan Tray	80 mm
24828-305		119 mm	Fan Unit	Interscale	Fan Tray	119 mm
24828-307		119 mm	Fan Unit	Interscale	Fan Tray	119 mm
24830-101		80 mm	Fan Unit		Fan Tray	80 mm

Table 3/3

Catalog Number	Depth
24828-105	20 mm
24828-107	20 mm
24828-104	20 mm
24828-205	25 mm
24828-207	25 mm
24828-204	25 mm
24830-102	25 mm
24828-305	25 mm
24828-307	25 mm
24830-101	25 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER