

VARISTAR CP GLAZED DOOR WITH 3-POINT LOCKING

Glass door with 3 point locking allows stronger adhesion between door and the cabinet frame. This prevents the metal malleability to show and provides the door extra robustness.

FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/3

Catalog Number	Locking Type	Height	Product Type	Product Family	Works With	Type
21630-092	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-093	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-094	3-Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-095	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-096	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-097	3-Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-416	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-417	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-418	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-419	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-420	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-421	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-422	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-423	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-717	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Catalog Number	LockingType	Height	ProductType	Product Family	Works With	Type
21630-718	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-719	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-720	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-721	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-722	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-723	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-724	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-725	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-726	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-727	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-728	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Table 2/3						
Catalog Number	Rack Height	Width	Complies With	Color	Material	Finish
21630-092	42 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-093	47 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-094	52 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-095	42 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-096	47 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-097	52 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-416	24 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-417	24 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-418	29 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-419	29 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-420	33 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-421	33 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		

Catalog Number	Rack Height	Width	Complies With	Color	Material	Finish
21630-422	38 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-423	38 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey		
21630-717	24 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-718	24 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-719	29 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-720	29 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-721	33 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-722	33 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-723	38 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-724	38 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-725	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-726	42 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-727	47 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated
21630-728	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Powder Coated

Table 3/3		
Catalog Number	Color Code	Protection Rating
21630-092	RAL 7021	IP20
21630-093	RAL 7021	IP20
21630-094	RAL 7021	IP20
21630-095	RAL 7021	IP20
21630-096	RAL 7021	IP20
21630-097	RAL 7021	IP20
21630-416	RAL 7021	IP20
21630-417	RAL 7021	IP20
21630-418	RAL 7021	IP20
21630-419	RAL 7021	IP20
21630-420	RAL 7021	IP20
21630-421	RAL 7021	IP20
21630-422	RAL 7021	IP20
21630-423	RAL 7021	IP20
21630-717	RAL 7021	IP55
21630-718	RAL 7021	IP55

Catalog Number	Color Code	Protection Rating
21630-719	RAL 7021	IP55
21630-720	RAL 7021	IP55
21630-721	RAL 7021	IP55
21630-722	RAL 7021	IP55
21630-723	RAL 7021	IP55
21630-724	RAL 7021	IP55
21630-725	RAL 7021	IP55
21630-726	RAL 7021	IP55
21630-727	RAL 7021	IP55
21630-728	RAL 7021	IP55

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER