

VARISTAR CP STEEL DOOR, PERFORATED WITH 1-POINT LOCKING

Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

FEATURES

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

SPECIFICATIONS

Table 1/2

Catalog Number	Locking Type	Height	Product Type	Product Family	Works With	Type
21630-408	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-409	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-507	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-508	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-410	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-411	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-509	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-510	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-412	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-413	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated

Catalog Number	LockingType	Height	ProductType	Product Family	Works With	Type
21630-511	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-512	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-414	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-415	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-513	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-514	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-006	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-013	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-515	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-516	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-007	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-014	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-517	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-518	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-008	Single Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-015	Single Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated

Table 2/2						
Catalog Number	Rack Height	Width	Complies With	Color	Color Code	Protection Rating
21630-408	24 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-409	24 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-507	24 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20

Catalog Number	Rack Height	Width	Complies With	Color	Color Code	Protection Rating
21630-508	24 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-410	29 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-411	29 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-509	29 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-510	29 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-412	33 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-413	33 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-511	33 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-512	33 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-414	38 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-415	38 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-513	38 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-514	38 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-006	42 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-013	42 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-515	42 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-516	42 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-007	47 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-014	47 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-517	47 U	600 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-518	47 U	800 mm	IEC 61587-1	Black Grey	RAL 7021	IP20
21630-008	52 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-015	52 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER