

VARISTAR CP STEEL DOOR, PLAIN WITH 3-POINT LOCKING, IP20

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Locking Type	Height	Product Type	Product Family	Works With	Type
21630-104	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-105	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-106	3-Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-107	3-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-108	3-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-109	3-Point Locking	2450 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-432	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-433	3-Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-434	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-435	3-Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-436	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-437	3-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-438	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door
21630-439	3-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door

Table 2/2

Catalog Number	Rack Height	Width	Complies With	Color	Color Code	Protection Rating
----------------	-------------	-------	---------------	-------	------------	-------------------

21630-104	42 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-105	47 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-106	52 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-107	42 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-108	47 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-109	52 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-432	24 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-433	24 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-434	29 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-435	29 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-436	33 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-437	33 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-438	38 U	600 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20
21630-439	38 U	800 mm	IEC 61587-1, IEC 61587-3	Black Grey	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER