

EUROPACPRO 19" SUBRACK KIT FOR BACKPLANE, RETROFIT SHIELDING

Non-shielded subrack for backplane mounting.



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Depth	For Mounting	Board Depth	EMC Shielding
24563-131	3U	84HP	175mm	Backplane	160mm	No
24563-132	3U	84HP	235mm	Backplane	160mm, 220mm	No

Catalog Number	Rack Height	Rack Width	Depth	ForMounting	Board Depth	EMC Shielding
24563-133	3U	84HP	295mm	Backplane	160mm, 220mm, 280mm	No
24563-134	3U	84HP	355mm	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-135	3U	84HP	415mm	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-136	3U	84HP	475mm	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-431	6U	84HP	175mm	Backplane	160mm	No
24563-432	6U	84HP	235mm	Backplane	160mm, 220mm	No
24563-433	6U	84HP	295mm	Backplane	160mm, 220mm, 280mm	No
24563-434	6U	84HP	355mm	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-435	6U	84HP	415mm	Backplane	160mm, 220mm, 280mm, 340mm	No
24563-436	6U	84HP	475mm	Backplane	160mm, 220mm, 280mm, 340mm	No

Table 2/3						
Catalog Number	EMC Gasket Type	Static Load	Handle Included	Mounting	Complies With	Package Quantity
24563-131	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-132	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-133	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-134	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-135	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-136	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-431	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1

Catalog Number	EMC Gasket Type	Static Load	Handle Included	Mounting	Complies With	Package Quantity
24563-432	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-433	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-434	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-435	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1
24563-436	Stainless Steel (retrofittable)	11kgf	No	Rack	IEC 60297-3-103	1

Table 3/3		
Catalog Number	Finish	Material
24563-131	Anodized, Passivated	Aluminum
24563-132	Anodized, Passivated	Aluminum
24563-133	Anodized, Passivated	Aluminum
24563-134	Anodized, Passivated	Aluminum
24563-135	Anodized, Passivated	Aluminum
24563-136	Anodized, Passivated	Aluminum
24563-431	Anodized, Passivated	Aluminum
24563-432	Anodized, Passivated	Aluminum
24563-433	Anodized, Passivated	Aluminum
24563-434	Anodized, Passivated	Aluminum
24563-435	Anodized, Passivated	Aluminum
24563-436	Anodized, Passivated	Aluminum

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER