


FRONT PANEL, FLAT, UNSHIELDED, D-SUB CUTOUTS



Flat front panel with cutout for D-Sub connectors. Unshielded version.

CERTIFICATIONS



FEATURES

Non-shielded version

Al, 2.5 mm, front anodized, rear conductive

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3						
Catalog Number	Product Type	Туре	EMC Shielding	Material	Rack Height	Front Finish
30118-341	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized

Catalog Number	ProductType	Туре	EMC Shielding	Material	Rack Height	Front Finish
30118-342	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized
30118-343	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized
30118-344	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized
30118-345	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized
30118-346	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized
30118-347	Front Panel	Front Panel without Handle	No	Aluminum	3U	Anodized

Table 2/3						
Catalog Number	Rear Finish	Height (H)	Treated Edges	Rack Width	Width (W)	Depth (D)
30118-341	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-342	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-343	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-344	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-345	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-346	Conductive	128.4mm	No	4HP	19.98mm	2.5mm
30118-347	Conductive	128.4mm	No	4HP	19.98mm	2.5mm

Table 3/3						
Catalog Number	Mounting	Complies With	Package Quantity	Finish		
30118-341	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-342	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-343	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-344	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-345	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-346	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		
30118-347	Screw-on Front	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated		


ADDITIONAL PRODUCT DETAILS


Delivery is in standard pack multiples. Pricing is per individual item.


Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS







WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: schroff.nvent.com

Europe Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM **SCHROFF**