

## FRONT PANEL, UNSHIELDED, WITH FASTENER PIN



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

### CERTIFICATIONS



### FEATURES

Enable grounding of the front area (protection class 1)

### SPECIFICATIONS

**Accessory Type:** Front panel

Table 1/3

Catalog Number	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
20119-159	Front Panel without Handle	Screw-on Front	No	Aluminum	Anodized	Conductive
20119-160	Front Panel without Handle	Screw-on Front	No	Aluminum	Anodized	Conductive
20119-161	Front Panel without Handle	Screw-on Front	No	Aluminum	Anodized	Conductive
20119-162	Front Panel without Handle	Screw-on Front	No	Aluminum	Anodized	Conductive

Catalog Number	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
20119-163	Front Panel without Handle	Screw-on Front	No	Aluminum	Anodized	Conductive

Table 2/3

Catalog Number	Treated Edges	Rack Height	Height	Rack Width	Width	Depth
20119-159	No	3U	128.4mm	7HP	35.2mm	2.5mm
20119-160	No	3U	128.4mm	14HP	70.8mm	2.5mm
20119-161	No	3U	128.4mm	21HP	106.3mm	2.5mm
20119-162	No	3U	128.4mm	28HP	141.9mm	2.5mm
20119-163	No	3U	128.4mm	42HP	213mm	2.5mm

Table 3/3

Catalog Number	Complies With	Package Quantity	Finish
20119-159	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated
20119-160	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated
20119-161	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated
20119-162	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated
20119-163	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**