

ENLOGIC BASIC PDU



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

SPECIFICATIONS

Table 1/5

| Catalog Number | Product Type | Product Family | Switched Outlets | Type | Width | Package Quantity |
|----------------|--------------|----------------|------------------|-----------|-------|------------------|
| EB0860 | Socket Strip | Enlogic | No | Basic PDU | 56mm | 1 |
| EB09JA | Socket Strip | Enlogic | No | Basic PDU | 114mm | 1 |

Table 2/5

| Catalog Number | Socket Type | Socket Quantity | Color | Height | Material | Finish |
|----------------|---------------------------------------|-----------------|-------|--------|----------|---------------|
| EB0860 | (24) C13/C15, (24) C13/C15/C19/C21 | 48 | Black | 1490mm | Steel | Powder Coated |
| EB09JA | (18) C13/C15, (18) C13/C15/C19/C21 | 36 | Black | 965mm | Steel | Powder Coated |

Table 3/5

| Catalog Number | Depth | Nominal Voltage | Cable Length | Rack Units | Circuit Breaker Quantity | Current Rating |
|----------------|-------|-----------------|--------------|------------|--------------------------|----------------|
| EB0860 | 55mm | 415V | 3000m | 0U | 6 | 22.1kV·A |
| EB09JA | 75mm | 415V | 1800m | 0U | 12 | 43.5kV·A |

Table 4/5

| Catalog Number | On/Off Switch Included | Number of Output Voltages | Circuit Breaker | Metering Type | Nominal Power Output | Removable Input Cable |
|----------------|------------------------|---------------------------|-----------------------|---------------|----------------------|-----------------------|
| EB0860 | No | | 20 A, 1-pole, Hy-MagA | None | 230VAC | No |
| EB09JA | No | 36 | 20 A, 1-pole, Hy-MagA | None | 230VAC | No |

Table 5/5

| Catalog Number | Plug Type | Input Cable Length | Output Voltage |
|----------------|-----------------------|--------------------|----------------|
| EB0860 | IEC 60309 530P6/532P6 | 3m | 208 – 230VAC |
| EB09JA | IEC 60309 560P6/563P6 | 1.8m | 208 – 230VAC |

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER