


GUIDE RAIL END PIECE, PC

Plastic end pieces for individual multi-piece guide rails with plastic or Aluminum extrusion mid-piece. Available as type Standard or Accessory.



CERTIFICATIONS



FEATURES

Guide rail end pieces (PC) for individual multi-piece guide rails with plastic or aluminum extrusion mid-piece

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Mid-pieces available for standard PCB lengths (160, 220, 280 and 340 mm) and for special dimensions as 1000 mm version

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Works With	Complies With	Package Quantity	Package Unit	Material
64568-004	Standard	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic
64568-008	Accessory	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic

Catalog Number	Type	Works With	Complies With	Package Quantity	PackageUnit	Material
64568-014	Standard	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic
64568-018	Accessory	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic
64568-093	Coding Peg	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic
64568-094	Coding Peg	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic
64568-095	Coding Peg	Subracks, Cases, Chassis	EN 45545-2	1	Pair	Fiber-Reinforced Plastic

Table 2/2	
Catalog Number	Groove Width
64568-004	2
64568-008	2
64568-014	2.5
64568-018	2.5
64568-093	2.5
64568-094	2.5
64568-095	2.5

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER