



NVENT CADDY SPEED LINK SLK WITH LOOP



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

SPECIFICATIONS

Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel;Polypropylene;Zinc Alloy
Complies With:	SMACNA HVAC-DCS

Table 1/3

Catalog Number	Article Number	E-Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)
----------------	----------------	----------	--------------------	------------------	------------	------------

SLK15L1LP	196601	1568235	1.5 mm	1m	101.6 mm	55 mm
SLK15L1LPR2	196628		1.5 mm	1m	101.6 mm	55 mm
SLK15L2LP	196514	1568236	1.5 mm	2m	101.6 mm	55 mm
SLK15L2LPR2	196629	1568180	1.5 mm	2m	101.6 mm	55 mm
SLK15L3LP	196515	1568237	1.5 mm	3m	101.6 mm	55 mm
SLK15L3LPR2	196630	1568181	1.5 mm	3m	101.6 mm	55 mm
SLK15L5LP	196516	1568238	1.5 mm	5m	101.6 mm	55 mm
SLK15L7LP	196602	1568239	1.5 mm	7m	101.6 mm	55 mm
SLK2L10LP	196606	1568246	2 mm	10m	101.6 mm	55 mm
SLK2L1LP	196604	1568241	2 mm	1m	101.6 mm	55 mm
SLK2L2LP	196543	1568242	2 mm	2m	101.6 mm	55 mm
SLK2L3LP	196544	1568243	2 mm	3m	101.6 mm	55 mm
SLK2L5LP	196545	1568244	2 mm	5m	101.6 mm	55 mm
SLK3L10LP	196711	1568142	3 mm	10m	101.6 mm	62 mm
SLK3L2LP	196707	1568144	3 mm	2m	101.6 mm	62 mm
SLK3L3LP	196708	1568145	3 mm	3m	101.6 mm	62 mm
SLK3L5LP	196709	1568146	3 mm	5m	101.6 mm	62 mm


Table 2/3						
Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Angle (a)	Static Load (F)
SLK15L1LP	196601	1568235	19 mm	12.5 mm	90 ° Max	195N
SLK15L1LPR2	196628		19 mm	12.5 mm	90 ° Max	195N
SLK15L2LP	196514	1568236	19 mm	12.5 mm	90 ° Max	195N
SLK15L2LPR2	196629	1568180	19 mm	12.5 mm	90 ° Max	195N
SLK15L3LP	196515	1568237	19 mm	12.5 mm	90 ° Max	195N
SLK15L3LPR2	196630	1568181	19 mm	12.5 mm	90 ° Max	195N
SLK15L5LP	196516	1568238	19 mm	12.5 mm	90 ° Max	195N
SLK15L7LP	196602	1568239	19 mm	12.5 mm	90 ° Max	195N
SLK2L10LP	196606	1568246	19 mm	12.5 mm	90 ° Max	440N
SLK2L1LP	196604	1568241	19 mm	12.5 mm	90 ° Max	440N
SLK2L2LP	196543	1568242	19 mm	12.5 mm	90 ° Max	440N
SLK2L3LP	196544	1568243	19 mm	12.5 mm	90 ° Max	440N
SLK2L5LP	196545	1568244	19 mm	12.5 mm	90 ° Max	440N
SLK3L10LP	196711	1568142	24 mm	16 mm	90 ° Max	890N
SLK3L2LP	196707	1568144	24 mm	16 mm	90 ° Max	890N
SLK3L3LP	196708	1568145	24 mm	16 mm	90 ° Max	890N

Catalog Number	Article Number	E-Number	Width (W)	Thickness(T)	Angle (a)	Static Load (F)
SLK3L5LP	196709	1568146	24 mm	16 mm	90 ° Max	890N

Table 3/3

Catalog Number	Article Number	E-Number	Packing Quantity	Certifications
SLK15L1LP	196601	1568235	1.0000	cUL, UL, SMACNA
SLK15L1LPR2	196628		2.0000	cUL, UL, SMACNA
SLK15L2LP	196514	1568236	1.0000	cUL, UL, SMACNA
SLK15L2LPR2	196629	1568180	2.0000	cUL, UL, SMACNA
SLK15L3LP	196515	1568237	1.0000	cUL, UL, SMACNA
SLK15L3LPR2	196630	1568181	2.0000	cUL, UL, SMACNA
SLK15L5LP	196516	1568238	1.0000	cUL, UL, SMACNA
SLK15L7LP	196602	1568239	1.0000	cUL, UL, SMACNA
SLK2L10LP	196606	1568246	1.0000	cUL, UL, SMACNA
SLK2L1LP	196604	1568241	1.0000	cUL, UL, SMACNA
SLK2L2LP	196543	1568242	1.0000	cUL, UL, SMACNA
SLK2L3LP	196544	1568243	1.0000	cUL, UL, SMACNA
SLK2L5LP	196545	1568244	1.0000	cUL, UL, SMACNA
SLK3L10LP	196711	1568142	1.0000	SMACNA
SLK3L2LP	196707	1568144	1.0000	SMACNA
SLK3L3LP	196708	1568145	1.0000	SMACNA
SLK3L5LP	196709	1568146	1.0000	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER