

ATCA FRONT PANEL KIT WITH SPRING LOADING



AdvancedTCA front panel for spring-loaded IEA handle (plunger or lever style) with die-cast end piece in Al-Profile or stainless material.

CERTIFICATIONS



FEATURES

Front panel (reinforced with diecast endpiece)

ATCA IEA handle with spring loading

EMC textile gasket and fixing material

SPECIFICATIONS

Accessory Type: Front panel


Table 1/2

Catalog Number	Front Finish	Rear Finish	Material	Rack Height	Rack Width	Width (W)
20818-160	Raw	Raw	Stainless Steel	8U	6HP	28.95mm
20818-161	Raw	Raw	Stainless Steel	8U	6HP	28.95mm
20818-169	Raw	Raw	Aluminum	8U	6HP	28.95mm
20818-170	Raw	Raw	Aluminum	8U	6HP	28.95mm

Table 2/2

Catalog Number	Depth (D)	Height (H)	Package Quantity	Finish
20818-160	1mm	323.15mm	1	
20818-161	1mm	323.15mm	1	
20818-169	1mm	323.15mm	1	Passivated
20818-170	1mm	323.15mm	1	Passivated

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER