




NVENT CADDY PYRAMID 50 FOAM-BASED SUPPORT



FEATURES

- Replaces slow and labor-intensive installation methods
- Supports pipe, conduit, cable tray and equipment on roofs and below raised floors
- Easily increase load capacity by combining similar nVent CADDY Pyramid supports
- Protects the roof membrane while absorbing shock and vibration, without absorbing water
- Metal cover protects against weather and other environmental conditions, such as bird damage


SPECIFICATIONS

- Static Load Safety Factor:** 3:1
- Finish:** Electrogalvanized
- Material:** Steel;Polyethylene

Table 1/1

| Catalog Number | Article Number | Height (H) | Length (L) | Width (W) | Static Load (F) |
|----------------|----------------|------------|------------|-----------|-----------------|
| RPS50H4EG | 182470 | 101 mm | 264 mm | 101 mm | 220N |
| RPS50H6EG | 182480 | 152 mm | 264 mm | 127 mm | 220N |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER