

RACK-MOUNTABLE TRAY 19-INCH, 1UX12.52, BLACK, STEEL

CATALOG NUMBER

A19FT6B



Fan trays enhance the natural convection airflow within a cabinet when installed with other 19-inch rack-mount equipment.

FEATURES

Fan trays available with either three or six 4-inch fans

Includes 72-inch (1829-mm) power cord with IEC 320 standard power socket

Power cord plugs into standard 115 VAC outlet

Lighted rocker switch provides on-off control and indicates when fans are on

PRODUCT ATTRIBUTES

Article Number: 13856

Height: 42mm

Max m³/hr: 860m³/h

Width: 483mm

Fan Quantity: 6

Input Voltage AC: 100 – 120V

Depth: 329mm

Nominal Watts: 90W

Max Temperature: 70°C

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER