



NVENT CADDY ALL-IN-ONE BETWEEN-STUD WITHOUT MUD RING, SINGLE BOX



CERTIFICATIONS



FEATURES

- Provides the flexibility to add a mud ring for non-standard drywall thicknesses
- Box remains fixed in place when mud ring is removed
- Pre-bent tabs on support bracket help to quickly square assembly to stud
- Center marks provide easy height positioning
- Includes multiple 1/2 and 3/4 in knockouts on each side of the box
- Works with standard US and Canadian mud rings

SPECIFICATIONS

- Finish:** Pregalvanized
- Material:** Steel

Table 1/2						
Catalog Number	Knockout Sizes	Ground Wire Included	Box Volume	Stud Spacing	Depth (D)	A

A1BF0GS	(8) 1/2", 3/4", (3) 1/2"	Yes	32.8in ³	16" - 24"	2 1/2"	5 3/8"
A1BD0N	(5) 1/2", 3/4", (1) 1/2", (3) 1"	No	32.8in ³	16" - 24"	3 5/8"	5 3/8"
A1BF0G	(8) 1/2", 3/4", (3) 1/2"	Yes	32.8in ³	16" - 24"	3 5/8"	5 3/8"

Table 2/2

Catalog Number	B
A1BF0GS	4 1/8"
A1BD0N	4 1/8"
A1BF0G	4 1/8"



ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

24" stud spacing requires use of three mounting screws.

Use only with nVent CADDY All-in-One box assemblies.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER