



NVENT CADDY PYRAMID TOOL-FREE PIPE CLAMP



FEATURES

- Push-in clamps install without the need for additional tools or strut clamps
- Clamps come in two different sizes to fit project needs
- Plastic clamps and base will not corrode pipe

SPECIFICATIONS

- Material:** Nylon
- Temperature:** -50 to 150 °F

Table 1/1

Catalog Number	Outer Diameter (OD)	Length (L)	Width (W)	A	Unit Weight
PTF1C	1/2" - 1.32"	1.6"	3/4"	3/8"	0.03 lb
PTF2C	0.840" - 2.38"	3.2"	3/4"	3/8"	0.04 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support	Europe Netherlands: +31 800-0200135 France: +33 800 901 793	Europe Germany: 800 1890272 Other Countries: +31 13 5835404	APAC Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500
---	--	--	--