



## NVENT CADDY TELESCOPING RIGID BOX SUPPORT BRACKET BETWEEN STUD ASSEMBLY



### FEATURES

Accommodates up to 6-gang box in 16" stud spacing or up to 10-gang in 24" stud spacing

Open design allows a variety of positions for box location

Easy to adjust after the electrical box is installed

### SPECIFICATIONS

**Knockout Sizes, Box 2:** (12) 1/2", 3/4"

**Knockout Sizes, Box 1:** (4) 1/2", 3/4";(8) 1/2"

**Finish:** Pregalvanized

**Material:** Steel

Table 1/2

Catalog Number	Box Depth	Box Size 1	Box Size 2	Drywall Thickness	Gang, Box 1	Gang, Box 2
TR4DM1	2.12	4		3/4"	1	
TR4DM1P1M5	2.12	4	4 11/16"	3/4"	1	1

Table 2/2

Catalog Number	Ground Wire Included	Mud Ring Type	Stud Spacing	Volume, Box 1	Volume, Box 2
TR4DM1	Yes	Raised	16" - 24"	30.3in <sup>3</sup>	
TR4DM1P1M5	Yes	Raised	16" - 24"	30.3in <sup>3</sup>	42in <sup>3</sup>

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**