

CABLE TO WEB OF RAIL MOLD ONLY, POWER



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

SPECIFICATIONS

Material: Graphite

Bond Terminal Style: W

Table 1/2

Catalog Number	Rail Type	Handle Clamp	Conductor Outer Diameter, Nominal	Welder Style	Welding Material	Orientation
PBWH2LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.3in	T20	PB45 or PB45PLUSF80, Sold Separately	Left Hand
PBWH2RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.3in	T20	PB45 or PB45PLUSF80, Sold Separately	Right Hand
PBWX3RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.36in	T20	PB65, Sold Separately	Right Hand
PBW2CLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.37in	T20	PB65 or PB65PLUSF80, Sold Separately	Left Hand

Catalog Number	Rail Type	Handle Clamp	Conductor Outer Diameter, Nominal	Welder Style	Welding Material	Orientation
PBW2CRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.37in	T20	PB65 or PB65PLUSF80, Sold Separately	Right Hand
PBW2GLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.42in	T20	PB90, Sold Separately	Left Hand
PBW2GRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.42in	T20	PB90, Sold Separately	Right Hand
PBW2JLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.48in	T20	PB90 or PB90PLUSF80, Sold Separately	Left Hand
PBW2JRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.48in	T20	PB90 or PB90PLUSF80, Sold Separately	Right Hand
PBW2QLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.53in	T20	PB90 or PB90PLUSF80, Sold Separately	Left Hand
PBW2QRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.53in	T20	PB90 or PB90PLUSF80, Sold Separately	Right Hand
PBWS6LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.57in	T20	PB115 or PB115PLUSF80, Sold Separately	Left Hand
PBWS6RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.57in	T20	PB115 or PB115PLUSF80, Sold Separately	Right Hand
PBW2SLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.61in	T20	PB90 or PB90PLUSF80, Sold Separately	Left Hand
PBW2SRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.61in	T20	PB90 or PB90PLUSF80, Sold Separately	Right Hand
PBWX5LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.61in	T20	PB90 or PB90PLUSF80, Sold Separately	Left Hand
PBWX5RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.61in	T20	PB90 or PB90PLUSF80, Sold Separately	Right Hand
PBWX7LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.67in	T20	PB200 or PB200PLUSF80, Sold Separately	Left Hand

Catalog Number	Rail Type	Handle Clamp	Conductor Outer Diameter, Nominal	Welder Style	Welding Material	Orientation
PBWX7RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.67in	T20	PB200 or PB200PLUSF80, Sold Separately	Right Hand
PBW2W010LH	R13, RI52	C105C, Sold Separately	0.75in	T20	PB115, Sold Separately	Left Hand
PBW2W010RH	R13, RI52	C105C, Sold Separately	0.75in	T20	PB115, Sold Separately	Right Hand
PBW2WLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.75in	T20	PB115, Sold Separately	Left Hand
PBW2WLK1LH	LK1 Girder Rail	C105C, Sold Separately	0.75in	T20	PB115 or PB115PLUSF80, Sold Separately	Left Hand
PBW2WLK1RH	LK1 Girder Rail	C105C, Sold Separately	0.75in	T20	PB115 or PB115PLUSF80, Sold Separately	Right Hand
PBW2WRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.75in	T20	PB115, Sold Separately	Right Hand
PBWX8LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.8in	T20	PB200 or PB200PLUSF80, Sold Separately	Left Hand
PBWX8RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.8in	T20	PB200 or PB200PLUSF80, Sold Separately	Right Hand
PBW3FRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.88in	T20	PB150 or PB150PLUSF80, Sold Separately	Right Hand
PBWX902LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.93in	T20	PB250, Sold Separately	Left Hand
PBWX902RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	0.93in	T20	PB250, Sold Separately	Right Hand
PBW3S002LH	RI60	PBC105Q, Sold Separately	1.04in	T20	PB250, Sold Separately	Left Hand
PBW3S002RH	RI60	PBC105Q, Sold Separately	1.04in	T20	PB250, Sold Separately	Right Hand
PBW3SLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	1.04in	T20	PB250, Sold Separately	Left Hand
PBW3SLK1LH	LK1 Girder Rail	C105C, Sold Separately	1.04in	T20	PB250 or PB250PLUSF80, Sold Separately	Left Hand

Catalog Number	Rail Type	Handle Clamp	Conductor Outer Diameter, Nominal	Welder Style	Welding Material	Orientation
PBW3SLK1RH	LK1 Girder Rail	C105C, Sold Separately	1.04in	T20	PB250 or PB250PLUSF80, Sold Separately	Right Hand
PBW3SRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	1.04in	T20	PB250, Sold Separately	Right Hand

Table 2/2

Catalog Number	Conductor Size
PBWY2LH	35 mm ² Concentric
PBWY2RH	35 mm ² Concentric
PBWX3RH	50 mm ² Ropelay
PBW2CLH	1/0 Concentric
PBW2CRH	1/0 Concentric
PBW2GLH	2/0 Concentric
PBW2GRH	2/0 Concentric
PBW2JLH	2/0 Ropelay
PBW2JRH	2/0 Ropelay
PBW2QLH	4/0 Concentric
PBW2QRH	4/0 Concentric
PBWS6LH	3/0 Composite
PBWS6RH	3/0 Composite
PBW2SLH	4/0 Ropelay
PBW2SRH	4/0 Ropelay
PBWX5LH	95 mm ² Ropelay
PBWX5RH	95 mm ² Ropelay
PBWX7LH	150 mm ² Ropelay
PBWX7RH	150 mm ² Ropelay
PBW2W010LH	250 kcmil Ropelay
PBW2W010RH	250 kcmil Ropelay
PBW2WLH	250 kcmil Ropelay
PBW2WLK1LH	250 kcmil Ropelay
PBW2WLK1RH	250 kcmil Ropelay
PBW2WRH	250 kcmil Ropelay
PBWX8LH	185 mm ² Ropelay

Catalog Number	Conductor Size
PBWX8RH	185 mm ² Ropelay
PBW3FRH	350 kcmil Ropelay
PBWX902LH	240 mm ² Ropelay
PBWX902RH	240 mm ² Ropelay
PBW3S002LH	500 kcmil Ropelay
PBW3S002RH	500 kcmil Ropelay
PBW3SLH	500 kcmil Ropelay
PBW3SLK1LH	500 kcmil Ropelay
PBW3SLK1RH	500 kcmil Ropelay
PBW3SRH	500 kcmil Ropelay

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER