

PROLINE S1 RACK ANGLES, 2300X600MM, BLACK, STEEL

CATALOG NUMBER

PS1RA236



Rack angles are sold in pairs that are RU marked on all sides. One side is tapped 10-32 while the other side is square hole (.375 x .375 inch). Both sides are spaced per EIA universal standard. Rack angles may be assembled in either tapped or square-hole configuration. Rack angles and mounting brackets are formed from heavy gauge steel. All hardware and brackets are included for assembly into cabinet.

FEATURES

Rack angles are sold in pairs that are RU marked on all sides

One side is tapped 10-32 while the other side is square hole (.375 x .375 inch)

Both sides are spaced per EIA universal standard

Rack angles may be assembled in either tapped or square-hole configuration

Rack angles and mounting brackets are formed from heavy gauge steel

All hardware and brackets are included for assembly into cabinet

PRODUCT ATTRIBUTES

Article Number: 39247

Height: 90.55in

Width: 23.62in

Depth: 23.62in

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 12ga

Fits Cabinet: 2300x600in

Rack Units: 48U

Rack Spacing: 19-in.

Weight: 22.62lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER