


## OPEN FRAME RACK-MOUNT STEEL SHELF



The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment. It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg).

### FEATURES

The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment.

It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg).

### SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Style	Rack Units
EMS1918	13266	5.25in	19in	18in	Solid	3U
EMS1922	13267	5.25in	19in	22in	Solid	3U
EMSV1918	13271	5.25in	19in	18in	Vented	3U
EMSV1922	13268	5.25in	19in	22in	Vented	3U

Table 2/2

Catalog Number	Article Number	Finish	Material	Color	Color Code	Thickness
EMS1918	13266	Powder Coated	Mild Steel	Jet Black	RAL 9005	16ga
EMS1922	13267	Powder Coated	Mild Steel	Jet Black	RAL 9005	16ga
EMSV1918	13271	Powder Coated	Mild Steel	Jet Black	RAL 9005	16ga
EMSV1922	13268	Powder Coated	Mild Steel	Jet Black	RAL 9005	16ga

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**