

## PROLINE S1 RACK ANGLES



Rack angles are sold in pairs that are RU marked on all sides. One side is tapped 10-32 while the other side is square hole (.375 x .375 inch). Both sides are spaced per EIA universal standard. Rack angles may be assembled in either tapped or square-hole configuration. Rack angles and mounting brackets are formed from heavy gauge steel. All hardware and brackets are included for assembly into cabinet.

### FEATURES

Rack angles are sold in pairs that are RU marked on all sides

One side is tapped 10-32 while the other side is square hole (.375 x .375 inch)

Both sides are spaced per EIA universal standard

Rack angles may be assembled in either tapped or square-hole configuration

Rack angles and mounting brackets are formed from heavy gauge steel

All hardware and brackets are included for assembly into cabinet

### SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Width	Depth	Fits Cabinet	Rack Spacing	Rack Units
PS1RA126	36755	23.62in	26.62in	1200x600in	19-in.	24U
PS1RA127	36756	27.56in	27.56in	1200x700in	19- or 23-in.	24U
PS1RA217	36758	27.56in	27.56in	2100x700in	19- or 23-in.	45U
PS1RA218	36914	31.5in	31.5in	2100x800in	19- or 23-in.	45U
PS1RA237	39248	27.56in	27.56in	2300x700in	19- or 23-in.	48U
PS1RA238	39251	31.5in	31.5in	2300x800in	19- or 23-in.	48U
PS1RA216	36757	23.62in	23.62in	2100x600in	19-in.	45U
PS1RA236	39247	23.62in	23.62in	2300x600in	19-in.	48U

Table 2/3

Catalog Number	Article Number	Height	Material	Finish	Color	Color Code
PS1RA126	36755	47.24in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA127	36756	47.24in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA217	36758	82.68in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA218	36914	82.68in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA237	39248	90.55in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA238	39251	90.55in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA216	36757	82.68in	Mild Steel	Powder Coated	Jet Black	RAL 9005
PS1RA236	39247	90.55in	Mild Steel	Powder Coated	Jet Black	RAL 9005

Table 3/3

Catalog Number	Article Number	Thickness
PS1RA126	36755	12ga
PS1RA127	36756	12ga
PS1RA217	36758	12ga
PS1RA218	36914	12ga
PS1RA237	39248	12ga
PS1RA238	39251	12ga
PS1RA216	36757	12ga
PS1RA236	39247	12ga

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**