

## PROLINE S1 SERVER PACKAGE



ProLine S1 Server Package Cabinets are an economical solution for contractors, small computer rooms, schools, retail outlets, or smaller networks that require a general purpose cabinet to house servers, switches, cables and other communication equipment. Multiple sizes, configurations, and accessories give ProLine S1 Cabinets wide application flexibility. ProLine S1 Server Packages are a data center-ready solution designed to be configured in a row or stand-alone configuration. The cabinets feature airflow management and provide easy cable access/mounting provisions.

### INDUSTRY STANDARDS

UL 2416 Listed File Number E230874

cUL Listed per CSA 22.2 60950-1-07

UL 2416 Bonding and Grounding (with use of PGK grounding Kit)

EIA 310-D (RU – Rack Unit spacing, marking, and positioning)  
IEC 60529, IP20

### FEATURES

Top panel has four-corner brush strip cable entry

Internal airflow management

Cable management (750mm and 800mm wide models)

Plinth base

Ability to externally mount cable management (i.e. ladder rack)

Caster/leveler kit pre-installed

PDU mounting brackets included (qty 2 pair)

Joining kits included with “middle” configurations

### SPECIFICATIONS

<b>Color:</b>	Jet Black
<b>Material:</b>	Mild Steel
<b>Finish:</b>	Powder Coated
<b>Color Code:</b>	RAL 9005

Table 1/2

Catalog Number	Article Number	Width	Depth	Protection Rating	Rack Units	Height
PS1SPE21612B	39231	23.87in	47.17in	NEMA Type 1, IP20	45U	85.14in
PS1SPE217512B	39233	27.87in	47.17in	NEMA Type 1, IP20	45U	85.14in
PS1SPE21812B	39235	31.81in	47.17in	NEMA Type 1, IP20	45U	85.14in
PS1SPM21612B	39232	23.87in	47.17in	NEMA Type 1, IP20	45U	85.14in
PS1SPM217512B	39234	27.87in	47.17in	NEMA Type 1, IP20	45U	85.14in
PS1SPM21812B	39236	31.81in	47.17in	NEMA Type 1, IP20	45U	85.14in

Table 2/2

Catalog Number	Article Number	Vertical Cable Manager Accessory	Sides	Thickness	Style
PS1SPE21612B	39231	No	Locking panels	16ga	End Package
PS1SPE217512B	39233	Yes	Locking panels	16ga	End Package
PS1SPE21812B	39235	Yes	Locking panels	16ga	End Package
PS1SPM21612B	39232	No	Internal partition	16ga	Middle Package
PS1SPM217512B	39234	Yes	Internal partition	16ga	Middle Package
PS1SPM21812B	39236	Yes	Internal partition	16ga	Middle Package

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**