

## RACK-MOUNT ADJUSTABLE SHELF



The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles. The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement. There are both solid and vented models available. They fit 19- or 23-inch rack spacing and require only 1U of rack space. Please note the load rating is for 150 lb. (68 kg).

### FEATURES

The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles

The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement

There are both solid and vented models available

They fit 19- or 23-inch rack spacing and require only 1U of rack space

Please note the load rating is for 150 lb. (68 kg)

### SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Type	Length	Max Depth	Width	Size
P19SH68	47399	Solid	19.68in	30.71in	17.32in	19 in.
P19SH68B	47909	Solid	19.68in	30.71in	17.32in	19 in.
P19VSH68B	11053	Vented	19.68in	30.71in	17.32in	19 in.
P19SH810	47409	Solid	27.56in	38.58in	17.32in	19 in.
P19SH810B	47919	Solid	27.56in	38.58in	17.32in	19 in.
P19VSH810B	11054	Vented	27.56in	38.58in	17.32in	19 in.
P23SH68B	12955	Solid	19.68in	30.71in	21.32in	23 in.
P23SH810B	12956	Solid	27.56in	38.58in	21.32in	23 in.
P23VSH68B	11055	Vented	19.68in	30.71in	21.32in	23 in.
P23VSH810B	11056	Vented	27.56in	38.58in	21.32in	23 in.

Table 2/3

Catalog Number	Article Number	Fits Enclosure Depth Up To	Finish	Material	Color	Color Code
P19SH68	47399	31.5in	Powder Coated	Mild Steel	Light Gray	RAL 7035
P19SH68B	47909	31.5in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P19VSH68B	11053	31.5in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P19SH810	47409	39.37in	Powder Coated	Mild Steel	Light Gray	RAL 7035
P19SH810B	47919	39.37in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P19VSH810B	11054	39.37in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P23SH68B	12955	31.5in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P23SH810B	12956	39.37in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P23VSH68B	11055	31.5in	Powder Coated	Mild Steel	Jet Black	RAL 9005
P23VSH810B	11056	39.37in	Powder Coated	Mild Steel	Jet Black	RAL 9005

Table 3/3

Catalog Number	Article Number	Thickness
P19SH68	47399	14ga
P19SH68B	47909	14ga
P19VSH68B	11053	14ga
P19SH810	47409	14ga
P19SH810B	47919	14ga
P19VSH810B	11054	14ga
P23SH68B	12955	14ga
P23SH810B	12956	14ga
P23VSH68B	11055	14ga
P23VSH810B	11056	14ga

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**