

RACKPOWER SPOT LEAK DETECTION SENSOR



Spot Fluid Leak Sensor to detect punctual leak for nVent SCHROFF RackPower PDU's.

FEATURES

Spot Fluid Leak Sensor to detect punctual leak

5 m Connection Cable

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

Measuring Range < 2 MOHMS PER CM

SPECIFICATIONS

Table 1/1

Catalog Number	Product Type	Works With	Package Quantity	Height	Removable Input Cable	Plug Type
EA9111	Sensor	RackPower	1	12.2in	No	RJ45

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER