

SECURE DUAL W-LOCK POWER CORD



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Works With	Type	Package Quantity	Color
EP1314024X150	Cable	Enlogic	RackPower	Cable	150	Black
EP1314048X125	Cable	Enlogic	RackPower	Cable	125	Black
EP1314072X100	Cable	Enlogic	RackPower	Cable	100	Black
EP1314B24X150	Cable	Enlogic	RackPower	Cable	150	Blue
EP1314B48X125	Cable	Enlogic	RackPower	Cable	125	Blue
EP1314B72X100	Cable	Enlogic	RackPower	Cable	100	Blue
EP1314R24X150	Cable	Enlogic	RackPower	Cable	150	Red
EP1314R48X125	Cable	Enlogic	RackPower	Cable	125	Red
EP1314R72X100	Cable	Enlogic	RackPower	Cable	100	Red
EP1920024X100	Cable	Enlogic	RackPower	Cable	100	Black

Catalog Number	ProductType	Product Family	Works With	Type	Package Quantity	Color
EP1920048X75	Cable	Enlogic	RackPower	Cable	75	Black
EP1920072X50	Cable	Enlogic	RackPower	Cable	50	Black
EP1920B24X100	Cable	Enlogic	RackPower	Cable	100	Blue
EP1920B48X75	Cable	Enlogic	RackPower	Cable	75	Blue
EP1920B72X50	Cable	Enlogic	RackPower	Cable	50	Blue
EP1920R24X100	Cable	Enlogic	RackPower	Cable	100	Red
EP1920R48X75	Cable	Enlogic	RackPower	Cable	75	Red
EP1920R72X50	Cable	Enlogic	RackPower	Cable	50	Red

Table 2/2

Catalog Number	Height	Removable Input Cable	Plug Type
EP1314024X150	10.63in	No	C13/C14
EP1314048X125	10.63in	No	C13/C14
EP1314072X100	10.63in	No	C13/C14
EP1314B24X150	10.63in	No	C13/C14
EP1314B48X125	10.63in	No	C13/C14
EP1314B72X100	10.63in	No	C13/C14
EP1314R24X150	10.63in	No	C13/C14
EP1314R48X125	10.63in	No	C13/C14
EP1314R72X100	10.63in	No	C13/C14
EP1920024X100	10.63in	No	C19/C20
EP1920048X75	10.63in	No	C19/C20
EP1920072X50	10.63in	No	C19/C20
EP1920B24X100	10.63in	No	C19/C20
EP1920B48X75	10.63in	No	C19/C20
EP1920B72X50	10.63in	No	C19/C20
EP1920R24X100	10.63in	No	C19/C20
EP1920R48X75	10.63in	No	C19/C20
EP1920R72X50	10.63in	No	C19/C20

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER