

SYSPEND 180-MAX VERTICAL PANEL COUPLING



Syspend 180-Max Vertical Panel Coupling mounts a vertical tube to the back of an enclosure or screen using Video Electronics Standards Association (VESA) mounting. The coupling has mounting holes drilled for standard VESA 75 and 100 flange sizes. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The vertical panel coupling has a safety stop and maintenance-free bearings.

FEATURES

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Syspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFICATIONS

Material: Aluminum
Finish: Powder Coated

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Color	Color Code
S1MPCV	32778	10.07in	5.51in	4.72in	Jet Black	RAL 9005
S1MPCVG	32805	7.28in	4.72in	5.51in	Light Gray	RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.